



Tab material: Isotan (54%Cu,44%Ni,Mn)

All framed values will be used for dimension checking !

- Samples can deviate in the execution from the serie.

- Dimensions and tolerances can be specified only after the testing of the devices for the mass production definitely

|                |   |  |  |                                |   |  |  |              |                     |          |     |
|----------------|---|--|--|--------------------------------|---|--|--|--------------|---------------------|----------|-----|
| Rev.           | ○ |  |  | Rev.                           | ○ |  |  |              | Customer's Approval |          |     |
| Rev.           | ○ |  |  | Rev.                           | ○ |  |  |              | Date                |          |     |
| Rev.           | ○ |  |  | Rev.                           | ○ |  |  |              | Signature           |          |     |
| Titel:         |   |  |  |                                |   |  |  | Scale<br>2:1 | Drawn               | 24.11.06 | SRi |
| CR2032 MFR AH0 |   |  |  |                                |   |  |  |              | Checked             | 30.11.06 | BBö |
|                |   |  |  |                                |   |  |  |              | Approved            |          |     |
|                |   |  |  | CH-4452 Itingen<br>Switzerland |   |  |  | 3.9166.4-    |                     |          |     |